<ADDRESS> ADEKA CORPORATION 7-2-35, HIGASHI OGU, ARAKAWA-KU TOKYO 116-8554 JAPAN SALES TEL +81-3-4455-2833 FAX +81-3-3809-8232 R&D TEL +81-50-5518-4336 FAX +81-3-3809-8284

Date prepared: November 13, 2013 Date revised : September 20, 2017

-Hydro gelator -**ADEKA NOL GT-730**

ADEKA NOL GT-730 is a water soluble polymer which has urethane bond in the structure. It associates water molecule and show thickening effect on water by forming water gel. It is used for cosmetics as gelator.

ADEKA NOL GT-730 is diluted product of GT-700 with butylene glycol and water. Effective component of both products are same.









Features

- ✔ High-elastic / Springy water gel
- ✓ Salt tolerance
- ✔ BHT free

- ✓ Good spray discharge
- Good solubility in water

Table of ingredients

Compositions (wt%)
30
50
19.94
0.03
0.03

- 1) Carry-over ingredient, Catalyst for synthesis
- 2) Carry-over ingredient, Antioxidant



7-2-35 Higashi-ogu, Arakawa-ku, Tokyo, 116-8554 www.adeka.co.jp


Specification

Appearance	Light yellow to light yellow-brown, clear liquid
Viscosity(mPa·s) 3.3%aq.	2,000-6,000
рН 3.3%aq.	6.0-8.5
Cloud Point (°C) 3.3% aq.	60.0 ≤
Ignition Residue(%)*1,2	≤ 0.2
Heavy metal(ppm)* ²	≤ 20
Arsenic(ppm)*2	≤ 2


^{*1} Detection Limit <0.1%

Characteristics

Polymeric framework of GT-730 polymer



Gelation mechanism



GT-730 polymer is composed of hydrophobic segment and hydrophilic segment. It forms micelles like a flower in water.

Association between micelles occurs by adding more than a certain concentration of GT-730 polymer. Then it makes water gel.



^{*2} Certified Value (Analyzed two lots a year)

Dissolution method

The following conditions are examples to prepare 5%aq of GT-730 in lab-scale.


St	irring device	Temp.(°C)	r/min (rpm)	Time
Paddle	ddle	25	250	3 h
		50	230	1 h
Homo- mixer		25	4000 - 6000	20 min
	did	50	2000 - 4000	10 min
Disper	000	25	4000 - 6000	20 min
	000	50	2000 - 4000	10 min

GT-730 can make gel with a paddle mixer, homomixer and disper. Its gel keeps a viscosity under strong shear. <u>Ex.</u> By a disper for 2 h at 8,000rpm.



Gel properties

(i)Viscosity curve of GT-730 gel




GT-730 gel is thixotropic.

Therefore, the gel can be sprayed.




(ii)Viscosity vs. Concentration



Same viscosity is obtained when solid concentration is the same.

(iii)Self smoothing property

Immediately after mixing




30 seconds after mixing



GT-730 gel has surface smoothness.


(iv)Influence of temperature



The viscosity changes reversibly by temperature in $15 - 50^{\circ}$ C.

The irreversible separation is shown over 60°C due to reach cloud point.

(v)Influence of salts




Both inorganic and organic salt have no influence on the viscosity of GT-730 gel.




(vi)Influence of solvent

Formulation: GT-730 5%, Solvent X%, Water (95-X)%



The viscosity of the gel decreases gradually by adding the solvents such as glycols. (vii)Influence of surfactants

Formulation: GT-730 6.7% , Surfactant X% , Water (93.3-X)%



Product Name: ADEKA NOL GT-730

Typical surfactants which have strong surface activity like LAURETH-7, CETRIMONIUM CHLORIDE SODIUM LAURATE increase the viscosity of GT-730 gel until certain concentration. Then they decrease the viscosity.

Water soluble polymer like POLYQUATERNIUM-6 or pluronic type surfactants which have weak surface activity like POLOXAMER 184 have little effect on the viscosity of GT-730 gel. Water insoluble surfactants like GLYCERYL STEARATE make O/W emulsion. And they little

- Structure of the surfactants -

effect on the viscosity of GT-730 gel.

LAURETH-7

POLOXAMER 184

$$\begin{array}{c|c} & & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & & \\ & & \\ & & & \\ & &$$

x+z=26, y=30

X+2

GLYCERYL STEARATE

CETRIMONIUM CHLORIDE

POLYQUATERNIUM-6

SODIUM LAURATE

Product Name: ADEKA NOL GT-730

Regulatory Information

Area	Inventory	Status	
Japan	ENCS	Listed	
USA	TSCA	Listed	
Canada	DSL	Listed	
Australia	AICS	Listed	
Korea	KECL	Listed	
China	IECSC	Listed	
Cilila	IECIC	Listed	
Taiwan	TCSI	Listed	
Philippine	PICCS	Not Listed	
EU	REACH	Fully complying with REACH (e.g. Registration)	